

Hamry 3567, 580 01 Havl. Brod, Czech Republic tel + 420 569 433620, fax + 420 569 422144

e-mail: 1-cube @ 1-cube.com web site: www.1-cube.com

## **SAMPLE MILL SJ500**

Disc type mill for grinding samples without moisture loss.

## **FEATURES**

- Low or No Moisture Loss
- Compatible with reference oven analysis
- Compatible with NIR analysis
- Compatible with Falling Time analysis
- Adjustable Grinds Settings
- Low Noise Level
- Suitable for grains with up to 20% Oil

## **TECHNICAL DATA**

Discs Grinder Type

•	Motor Power	0.5 HP
•	Motor Speed	1400 rpm
	Grinding Discs	64mm
•	Grinding Capacity	10 to 14 Kg/h
•	Power Supply	220 - 250 volts
•	Weight	12.5 Kg
•	Depth	0.28 m
•	Width	0.18 m
•	Height	0.57 m



## TYPICAL PARTICLE SIZE DISTRIBUTION

(with setting to fine grinding)

Aperture of sieve % of sample passing

through

710 μm
500 μm
210 μm
66.8

The SJ500 performs a particle size distribution compatible with various type of analysis or products, according to the setting of the distance between the discs (e.g. fine for Falling time, Near Infrared and coarse for Oven dry analysis).

The grinding discs are made from hard metal and easily replaceable.